Since 1968



User Manual

Wire Intercom CM-800/801



www.commax.com

COMMAX Co.,Ltd.

Thank you for purchasing COMMAX products.
Please carefully read this User's Guide (in particular, precautions for safety) before using a product and follow instructions to use a product exactly.
The company is not responsible for any safety accidents caused by abnormal operation of the product.









acy CALL Button

(CM-800)



- 2-1. Master Station CM-801
- After pressing on/off button of CM-801, pushing [call]button will making a call to CM-800.
- When receiving a call from the CM-800, pressing "Talk" button of CM-801 will make a conversation with CM-800 and releasing "Talk" button will hear voice from CM-800.
- 3) When CM-800 makes a call to CM-801, you can hear call sound.
- * * When the conversation is finished, make sure of pressing " ON/OFF " button.
- 2-2. Sub Station CM-800
- 1) Pressing "Call" button hear call sound from CM-801.
- 2) You can talk with CM-801 without any operating.
- 3) Pressing "Privacy" button to stop delivering the voice from CM- 800 to CM-801.



3. Installation & Wiring



CM-801 terminal of backside



4. Specification

** 12Voltage/1A power supply is recommendable to use for this products Wiring method		
1) Terminal 1 : Connecting with CM–800, Non–Polarity, Max. distance 300m		
2) Terminal 2 : Connecting with CM-800, Non-Polarity. Max,distance 300m		
 3) Terminal 3 : Connecting with Power supply. + 4) Terminal 4 : Connecting with Power supply 		

Item	Description		
Wire	With CM-800 : 2 wires (Talk 2)		
Rated Voltage	DC12V/ 200mA		
Transmission way	Half-Duplex		
Consumption	Standby: 7mA (In the status of connecting with CM-800) Max. : 160mA (In the status of connecting with CM-800)		
Distance	Between CM-801 and CM-800 Max. 300m / 0.65mm- copper wire		
Warranty Period	1 year		
Environment Condition	Storage Temperature Storage Humidity	-40 °C to 50 °C Less than 90 %	
Product Life-Cycle	10 years		



COMMAX Co.,Ltd.

513-11, Sangdaewon-dong, Jungwon-gu, Seongnam-si, Gyeonggi-do, Korea Int'l Business Dept. : Tel.; +82-31-7393-540~550 Fax.; +82-31-745-2133 Web site : www.commax.com

Printed In Korea / 2008. 10